

Impedance Analyzer IM3570 option

Frequency


sweep

mode

# **Enabling Simple Circuit Analysis and** Detailed Acceptance/Rejection Decision-Making

The Equivalent Circuit Analysis Firmware IM9000 is an optional function that enables equivalent circuit analysis using the Impedance Analyzer IM3570. Five typical


equivalent circuit analysis models and the analysis results can be used to calculate the ideal frequency characteristics and check the differences from the measured values. Furthermore, Cole-Cole plot, admittance circle, and other graphs can be displayed. Impedance Analyzer IM3570



rejection decision for

equivalent

circuit elements Analysis results simulation Cole-Cole plot and admittance circle display



#### Simple:

#### **Automatic Selection of Equivalent Circuit Model**

The IM9000 can automatically select the equivalent circuit model from the five typical models to minimize the differences between the measured values and the ideal frequency characteristics derived from the analysis results.

#### Detailed:


### **Acceptance/Rejection Decision for Elements Comprising Part**

An acceptance/rejection decision can be made for the L, C, and R elements comprising a part and the resonance sharpness (mechanical quality coefficient). A detailed decision can be made on the elements using the resonance of a piezoelectric element or inductor.

# Equivalent Circuit Analysis Firmware IM9000 Specifications

## Equivalent Circuit Model and Measurement Items

#### **■** Three-element model



#### ■ Measurement items (Three-element model)

L1 (Inductance)

C1 (Capacitance)


R1 (Resistance)

Qm (Resonance sharpness)

fr (Resonance frequency) /

fa (Anti-resonance frequency)

#### **■** Four-element model



#### ■ Measurement items (Four-element model)

L1 (Inductance)

C1 (Capacitance)

R1 (Resistance)

C0 (Parallel capacitance)

Qm (Resonance sharpness or mechanical quality coefficient)

fr (Resonance frequency)

fa (Anti-resonance frequency)


fs (Series resonance frequency)

fp (Parallel resonance frequency)

fm (Maximum admittance frequency)

fn (Minimum admittance frequency)

f1 (Maximum susceptance frequency) f2 (Minimum susceptance frequency)



Parameters of the 4-element model

#### Other functions

Circuit model selection	AUTO (automatic selection) / HOLD (fixed)
Estimation execution	AUTO (estimation is executed after frequency sweep ends) / MANUAL (estimation is executed by the user)
Sweep range using estimation	Normal sweep: Analysis is performed in the sweep range from the analysis start frequency to the analysis end frequency Segment sweep: Analysis is performed in the sweep range of the set segment number
Simulation	Enables displaying and comparing the ideal frequency characteristics graph derived from the analysis results or the values specified by the user

Comparator	Runs a comparator on the analysis results and outputs the decision results to LCD, EXT. I/O R1, L1, C1, C0, Qm: HI/IN/LO, absolute value setting
Display position of estimation results	Select the display position from upper, lower, left or right
X-Y display	Cole-Cole plot:  Set Rs to the first measurement item, X to the third measurement item, reverse the polarity of the third measurement item, and set correction coefficient A =-1 for scaling correction  Admittance circle display:  Set G to the first measurement item and B to the third measurement item



#### Model: EQUIVALENT CIRCUIT ANALYSIS FIRMWARE IM9000

Model No. (Order Code) (Note)

IM9000 (Factory option firmware for the IM3570)

The Equivalent Circuit Analysis Firmware IM9000 is an optional function for the Impedance Analyzer IM3570. The IM9000 is not included in the standard package. If you want to use the IM9000 function, specify the option upon purchase.

Customers who have purchased the Impedance Analyzer IM3570 can add the Equivalent Circuit Analysis Firmware IM9000 function. Please contact your local HIOKI representative

Note: Company names and Product names appearing in this catalog are trademarks or registered trademarks of various companies



**HEADQUARTERS** 81 Koizumi, Ueda, Nagano, 386-1192, Japan TEL +81-268-28-0562 FAX +81-268-28-0568 http://www.hioki.com/ E-mail: os-com@hioki.co.jp

# HIOKI (Shanghai) SALES & TRADING CO., LTD. TEL +86-21-63910090 FAX +86-21-63910360

http://www.hioki.cn / E-mail: info@hioki.com.cn

HIOKI SINGAPORE PTE. LTD.

TEL +65-6634-7677 FAX +65-6634-7477 E-mail: info-sg@hioki.com.sg

#### HIOKI KOREA CO., LTD.

TEL +82-2-2183-8847 FAX +82-2-2183-3360 E-mail: info-kr@hioki.co.jp

#### HIOKI USA CORPORATION

TEL +1-609-409-9109 FAX +1-609-409-9108 http://www.hiokiusa.com / E-mail: hioki@hiokiusa.com

DISTRIBUTED BY